

## HDMI over Dual Cat5/Cat6 Extender Kit, Wallplate Transmitter and Receiver for Video and Audio, 1920x1200 1080p at 60Hz (HDMI M/F)

MODEL NUMBER: **B125-101-60-WP**



### Description

Tripp Lite's HDMI Over Dual Cat5 Extender Wallplate Kit is the perfect solution for those who need to extend a HDMI signal over a long distance over two Cat5/6 cables.

- When using 24Awg, Solid Wire Cat6 cable, a 1080p @ 60Hz (or 1920 x 1200) signal can be extended up to 125 ft. from the source.
- When using 24Awg, Solid Wire Cat6 cable, a 3D signal can be extended up to 100 ft.
- When using 24Awg, Solid Wire Cat5 cable, a 1080p @ 60Hz (or 1920 x 1200) signal can be extended up to 75 ft. from the source.
- When using 24Awg, Solid Wire Cat5 cable, a 3D signal can be extended up to 50 ft.

Simply run two Cat5/6 cables between the local transmitter and remote receiver units, and plug in standard Tripp Lite HDMI cables to the HDMI source and the display.

The B125-101-60-WP comes with both local transmitter and remote receiver wallplates. DTS-HD, Dolby True HD and 7.1 Channel Surround Sound audio are supported, and it is compliant with HDCP, EDID and DDC. 24-bit True Color (8-bits per channel) is supported. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

### Features

- Extends a 1080p @ 60Hz (or 1920 x 1200) signal up to 125 ft. using 24Awg, Solid Wire Cat6 cabling (Tripp Lite N202-Series)
- Extends a 1080p @ 60Hz (or 1920 x 1200) signal up to 75 ft. using 24Awg, Solid Wire Cat5 cabling
- Extends a 3D signal up to 100 ft. using 24Awg, Solid Wire Cat6 cabling, or up to 50 ft. using 24Awg, Solid Wire Cat5 cabling
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- Supports HDCP, EDID and DDC
- Supports 24-bit True Color (8-bits per channel)

### Highlights

- Extends a 1080p @ 60Hz (or 1920 x 1200) signal up to 125 ft. using 24Awg, Solid Wire Cat6\* cabling (Tripp Lite N202-Series)
- Extends a 3D signal up to 100 ft. using 24Awg, Solid Wire Cat6\* cabling (Tripp Lite N202-Series)
- Supports 24-bit True Color (8-bits per channel)
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- Supports HDCP, EDID and DDC
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

\*When using Cat5 cable, the maximum extension distance is reduced by 50 ft.

### Package Includes

- Local Transmitter and Receiver Units
- External Power Supply ( Input: 100-240V, 50/60Hz, 0.5A - Output: 5V, 2A )
- Screwdriver for Equalization adjustment
- Wallplate screws
- Owners Manual



- Use Tripp Lite P568-Series HDMI cables to connect to HDMI source and monitor
- Equalization control dial for skew compensation
- Supports Lip-Sync Pass Through, and CEC pass through
- Green LED indicate power being received
- Orange LED indicates signal connection
- Compliant with the Federal Trade Agreements Act ( TAA ) for GSA schedule purchases

## Specifications

OVERVIEW	
Display Style	Extender
Cable Type	HDMI
CONNECTIONS	
Connector A	HDMI (FEMALE)
Connector B	RJ45 (FEMALE) (X2)
Ports	1
SPECIAL FEATURES	
Chromebook Compatible	Yes
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>