

1x2 HDMI over Cat5/Cat6 Extender Kit, Box-Style Transmitter and Receiver

MODEL NUMBER: **B126-2A1**



Description

The B126-2A1 transmits a 1080p (60Hz) signal to a monitor up to 150 ft. away using Cat5e/6 cable, where the Receiver then splits out to two HDMI ports, allowing two screens to show the source image. To achieve maximum distance and resolution, use 24Awg Solid Wire Cat5e/6 cable. (Tripp Lite's N202-Series) The transmitter unit features an HDMI port for the connection of a local monitor. The receiver unit features a built-in Equalization control for adjustment of the video image. Supports 24-bit True Color (8-bits per channel), HDCP, 3D, and both stereo audio and 7.1 channel surround sound audio (7.1 channel surround sound signal will be Multi-Channel or PCM). Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Installation Description

Installation is simple. Connect the transmitter unit to an HDMI source using a Tripp Lite P568-Series HDMI cable (not included). Connect the receiver unit to two displays using a Tripp Lite P568-Series HDMI cable (not included). Finally, connect the receiver to the RJ45 port on the transmitter using a single Cat5e/6 cable:

- A 1080p (60Hz) signal can be transmitted up to 150 ft.
- A 1080i (60Hz) signal can be transmitted up to 200 ft.
- A 3D signal can be transmitted up to 125 ft.

Further extend the signal range or add more displays by using a Tripp Lite Remote Repeater unit:

- Add up to three repeaters, with a receiver unit located at the end of the installation, for a total of 4 displays.
- A 1080p (60Hz) signal can be extended up to 125 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 1080p (60Hz) signal can be extended up to 500 ft..
- A 1080i (60Hz) signal can be extended up to 175 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 1080i (60Hz) signal can be extended up to 700 ft..
- A 3D signal can be extended up to 100 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 3D signal can be extended up to 400 ft..

Highlights

- Transmitter and Receiver Kit
- Receiver splits to 2 x HDMI ports for two TV connections
- 1080p up to 150ft, 1080i up to 200ft
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- B126-2A1 Kit (Transmitter and Receiver)
- External Power Supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A)
- Mounting Hardware
- Screwdriver for Equalization Adjustment
- Owner's Manual



Features

- Connect two TVs to a single HDMI video source over a single Cat5e/6 cable
- Extends an HDMI signal to 2 monitors up to 200 ft. from the source over a single Cat5e/6 cable
- Extends a 1080p (60Hz) signal up to 150 ft. from the source using Cat6 cabling, or up to 125 ft. using Cat5e cabling
- Extends a 1080i (60Hz) signal up to 200 ft. from the source using Cat6 cabling, or up to 175 ft. using Cat5e cabling
- Use 24 AWG, solid wire Cat5e/6 cable, such as Tripp Lite's N202-Series, to achieve maximum distance and resolution
- Further expand the range and number of monitors by adding B126-110 repeater units
- Add up to three repeaters on each Cat5e/6 channel, for a total of 4 displays per channel (An Active Remote Receiver should be the last unit in a channel)
- A 1080p (60Hz) signal can be extended up to 125 ft. for each repeater added into a channel (or up to 175 ft. for a 1080i (60Hz) signal when using either Cat5e or Cat6 cabling)
- Supports 24-bit True Color (8-bits per channel)
- Built-in equalization control to adjust the video image
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
Display Style	Extender
Cable Type	HDMI; UTP (Cat5, Cat5e, Cat6, Cat6a)
PHYSICAL	
Included Mounting Accessories	Yes
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
CONNECTIONS	
Connector A	HARDWIRE
Connector B	HARDWIRE
Ports	2
SPECIAL FEATURES	
Chromebook Compatible	Yes
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	1-year limited warranty
-------------------------------------	-------------------------

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>