

2-Port VGA with Audio over Cat5/Cat6 Extender Splitter, Box-Style Transmitter with EDID, 1920x1440 at 60Hz, Up to 1000-ft.

MODEL NUMBER: **B132-002A-2**



Description

Tripp Lite's B132-002A-2 allows you to split a single VGA Video and Audio signal into 2. Along with a B132-100A or B132-100A-WP-1 remote receiver unit, you can extend a 1920 x 1440 (60Hz) Video and Audio signal up to 500 ft., or a 1024 x 768 (60Hz) Video and Audio signal up to 1,000 ft., when using 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N022-01K-GY (Cat5) and N222-01K-GY (Cat6).

The range and number of monitors/speakers can be further expanded by adding B132-110A repeater units. Connect up to 4 remote units in a repeater chain (3 repeaters and 1 receiver), with a set of monitor and speakers at each location. A 1920 x 1440 (60Hz) Video and Audio signal can be extended up to 500 ft. from the first repeater in the chain to the last receiver. A 1024 x 768 (60Hz) Video and Audio signal can be extended up to 1,000 ft. from the first repeater in the chain to the last receiver.

For optimal video image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite P524-01K.

The transmitter unit features functionality that allows for the EDID information from a connected display to be copied and sent to the connected computer, providing optimal compatibility. Includes mounting hardware that allows unit to be wall mounted, rack mounted or pole mounted. Ideal for digital signage situations, such as retail, schools, churches, etc. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Splits a single VGA Video and Audio signal into 2
- A B132-100A or B132-100A-WP-1 remote receiver unit is required for each connected monitor
- Extends a 1920 x 1440 (60Hz) Video and Audio signal up to 500 ft., or a 1024 x 768 (60Hz) Video and Audio signal up to 1,000 ft., when using 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N022-01K-GY (Cat5) and N222-01K-GY (Cat6)
- Support for video resolutions up to 1920 x 1440 (60Hz)
- EDID copy feature ensures optimal display compatibility

Highlights

- Splits a single VGA Video and Audio signal into 2
- EDID copy feature ensures optimal display compatibility
- Extends a 1920 x 1440 (60Hz) Video and Audio signal up to 500 ft., or a 1024 x 768 (60Hz) Video and Audio signal up to 1,000 ft., when using 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N022-01K-GY (Cat5) and N222-01K-GY (Cat6)
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite P524-01K
- Can further expand the range and number of monitors/speakers by adding B132-110A repeaters
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- 2 Port Extender/Splitter local (Transmitter) unit
- Mounting hardware
- External Power Supply (Input: 100-240V, 50/60Hz, 1.5A Output: 12.6V, 3A)
- Owner's Manual



- Can further expand the range and number of monitors/speakers by adding B132-110A repeaters
- Connect up to 4 remote units in a repeater chain (3 repeaters and 1 receiver), with a set of monitor and speakers at each location
- A 1920 x 1440 (60Hz) Video and Audio signal can be extended up to 500 ft. from the first repeater in the chain to the last receiver. A 1024 x 768 (60Hz) Video and Audio signal can be extended up to 1,000 ft. from the first repeater in the chain to the last receiver.
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite P524-01K
- Includes mounting hardware that allows unit to be wall mounted, rack mounted or pole mounted.
- Ideal for digital signage situations, such as retail, schools, churches, etc.
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
Display Style	Splitter
Cable Type	UTP (Cat5, Cat5e, Cat6, Cat6a); VGA
PHYSICAL	
Shipping Weight (lbs.)	1.1
Shipping Weight (kg)	0.5
Unit Dimensions (hwd / in.)	1 x 2.5 x 3.7
Unit Dimensions (hwd / cm)	2.54 x 6.35 x 9.40
Unit Weight (lbs.)	0.45
Unit Weight (kg)	0.20
Color	Black
CONNECTIONS	
Connector A	HD15 (FEMALE)
Connector B	3.5MM (FEMALE)
Connector C	RJ45 (FEMALE) (X2)
Ports	2
SPECIAL FEATURES	
Chromebook Compatible	No
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>