

HDMI over Cat5/Cat6 Passive Extender, Box-Style Remote Receiver for Video and Audio, 1920x1200 1080p at 60Hz

MODEL NUMBER: **B126-1P0**



Description

The B126-1P0 is a receiver unit that is used with the B126-002 and B126-004 transmitter units. It extends a 1080p (60Hz) signal to a monitor up to 50 ft. away using Cat5e/6 cable. To achieve maximum distance and resolution, use 24Awg Solid Wire Cat5e/6 cable. (Tripp Lite's N202-Series) No power is required, and its built-in HDMI male connector plugs directly into a monitor without the need for an additional cable. Supports 24-bit True Color (8-bits per channel), HDCP, 3D, and both stereo audio and 7.1 channel surround sound audio (7.1 channel surround sound signal will be Multi-Channel or PCM).

Installation is simple. Connect the transmitter unit to an HDMI source using a Tripp Lite P568-Series HDMI cable (not included). Connect the built-in HDMI connector on the receiver unit directly to a display. Finally, connect the receiver to the RJ45 port on the transmitter using a single Cat5e/6 cable.

- A 1080p (60Hz) signal can be transmitted up to 50 ft.
- A 1080i (60Hz) signal can be transmitted up to 100 ft.
- Cannot be used for a 3D signal

Features

- For use with B126-002 and B126-004 transmitter units.
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p (60Hz)
- 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N202-Series, is required to achieve maximum distance and resolution.
- Use Tripp Lite P568-Series HDMI cables to connect to HDMI source.
- HDCP and 3D compatible.
- Compatible with both stereo audio and 7.1 channel surround sound audio (7.1 channel surround sound signal will be Multi-Channel or PCM).
- Supports 24-bit True Color (8-bits per channel).
- No external power required.
- Compatible with all operating systems.

Highlights

- For use with the and B126-004 transmitter units
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p (60Hz)
- HDCP and 3D compatible
- Compatible with both stereo audio and 7.1 channel surround sound audio (7.1 channel surround sound signal will be Multi-Channel or PCM)
- Supports 24-bit True Color (8-bits per channel)
- No external power required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- B126-1P0 HDMI Over Cat5 Passive Extender Remote Unit
- Owner's manual



- Plug and play; No drivers required.
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Specifications

OVERVIEW	
Display Style	Splitter
Cable Type	HDMI; UTP (Cat5, Cat5e, Cat6, Cat6a)
PHYSICAL	
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
CONNECTIONS	
Connector A	RJ45 (FEMALE)
Connector B	HDMI (MALE)
Ports	1
SPECIAL FEATURES	
Chromebook Compatible	Yes
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>