

HDMI with Serial and IR Over Cat5/Cat6 Extender Kit, Extended Range Transmitter and Receiver, 3840 x 2160 4Kx2K UHD 1080p up to 60Hz

MODEL NUMBER: **B126-1A1SR**



Description

The B126-1A1SR transmits HDMI, IR Remote, and Serial RS232 up to 328 ft. (100 m.) using a single Cat5e/6/6a cable. It supports Ultra High Definition (UHD) 4Kx2K video resolutions up to 3840 x 2160 @ 24Hz, HDCP and 3D compliant, and supports 7.1 channel surround sound, DTS-HD, and Dolby TrueHD audio. RS232 connection allows for use with scanners and touch-screen monitors, supporting Baud rates up to 115kbps full duplex. IR functionality allows you to use your HDMI source's remote control in the same location as your extended monitor/TV. (IR frequency @ 39Khz) Kit includes mounting hardware to be wall mounted, rack mounted, or pole mounted. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Cable Requirements

When extending a 3840 x 2160 @ 24Hz Ultra High Definition (UHD) 4Kx2K video signal, use the following cables (sold separately):

- Cat6A (available from Tripp Lite as a custom order) for up to 328 ft. (100 m.)
- Cat6 cable (24AWG, Solid Wire cable required, such as Tripp Lite's N202-Series) for up to 230 ft. (70 m.)
- Cat5e cable (26AWG, Solid Wire cable required, such as Tripp Lite's N001- and N002-Series) for up to 150 ft. (45.7 m.)

When extending computer video resolutions of 1920 x 1200 @ 60Hz, or HD video resolutions of 1080p @ 60Hz, use Cat5e/6 cable (24AWG, Solid Wire cable required, such as Tripp Lite's N202-Series) to extend the signal up to 328 ft. (100 m.).

Features

- Supports Ultra High Definition (UHD) 4Kx2K video resolutions up to 3840 x 2160 @ 24Hz
- Extend a 3840 x 2160 @ 24Hz signal up to 328 ft. (100 m.) using Cat6a cable (available from Tripp Lite as a custom order)

Highlights

- Supports Ultra High Definition (UHD) 4Kx2K video resolutions up to 3840 x 2160 @ 24Hz
- Supports 7.1 channel surround sound, DTS-HD, and Dolby TrueHD audio
- IR functionality allows you to use your HDMI source's remote control in the same location as your extended monitor
- Supports RS232 Serial baud rates up to 115kbps full duplex, for control of devices such as touchscreens or scanners
- HDCP and 3D compatible
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- Local Transmitter and Remote Receiver Units
- Two sets of IR-IN Cables
- Two sets of IR-OUT Cables
- 3.5 mm Male-to-DB9-Female Adapter Cable
- 3.5 mm Male-to-DB9-Male Adapter Cable
- Two sets of External Power Supplies (Input: 100-240V, 50/60 Hz, 0.5A Output: 5V, 2A)
- Two sets of Mounting Hardware Kits
- Owner's Manual



- Extend a 3840 x 2160 @ 24Hz signal up to 230 ft. (70 m.) using Cat6 cable (24AWG, Solid wire cable required, such as Tripp Lite's N202-Series)
- Extend a 3840 x 2160 @ 24Hz signal up to 150 ft. (45.7 m.) using Cat5 cable (26AWG, Solid wire cable required, such as Tripp Lite's N001- and N002-Series)
- Extends a computer video signal of 1920 x 1200 @ 60Hz, or a HD signal of 1080p @ 60Hz, up to 328 ft. (100 m.) using Cat5e/6 patch cable (24AWG, Solid wire cable required, such as Tripp Lite's N202-Series)
- IR functionality allows you to use your HDMI source's remote control in the same location as your extended monitor
- Uses an IR frequency of 39 KHz
- Extend a full duplex RS232 serial signal, such as from a touchscreen monitor, up to 328 ft. (100m) from the source
- Supports RS232 serial baud rates up to 115kbps full duplex
- Supports 7.1-channel surround sound, DTS-HD and Dolby True HD audio
- HDCP and 3D compatible
- Plug and play; no software or drivers required
- Includes mounting hardware, allowing each unit to be wall mounted, rack mounted or pole mounted
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
Display Style	Extender
Cable Type	HDMI; UTP (Cat5, Cat5e, Cat6, Cat6a)
PHYSICAL	
Included Mounting Accessories	Y
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
CONNECTIONS	
Connector A	HDMI (FEMALE)
Connector B	RJ45 (FEMALE)
Ports	1
SPECIAL FEATURES	
Chromebook Compatible	Yes
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	1-year limited warranty
-------------------------------------	-------------------------

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>