

Smart 232 32-Port Multi-User Cat5 KVM Switch for Rack Environments

MODEL NUMBER: 0SU22091



Description

Multi-user access and control of many computers/servers

The Smart 232, also available with 16 ports (Smart 216), is a high-performance KVM switch enabling multi-user access, control and management of multiple servers. It allows two users to control up to 32 mixed-platform (PS/2 & USB) servers. It also provide seamless power control via RPS.

Straightforward set up

Easy installation via user friendly OSD and LAN.

Space saving devices that eliminate cable clutter

The Smart 232 is a thin 1U sized, rack-mountable device that saves critical space in crowded server room environments. It features KVM over CAT5 technology that directly connects the switch to each computer in the server room via a ROC dongle, eliminating cable clutter and extending the distance between server and switch up to 30m/100ft.

From server rooms to data centers

Thanks to their advanced functionality the Smart 216 and Smart 232 overcome many of the challenges facing today's crowded server rooms and data centers. They are the ideal solution for corporate server rooms requiring both a powerful and versatile KVM solution.

Features

- 32 Ports with 2 simultaneous KVM Users
- BIOS level access
- USB keyboard and mouse console

Highlights

- 32 Ports with 2 simultaneous KVM Users
- BIOS level access
- USB keyboard and mouse console
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule Purchases

System Requirements

Operating System

- Windows, Novell, Linux, SUN Solaris

Resolution

- Supports video resolutions up to 1600 x 1200 @ 85Hz

Package Includes

- Smart 232
- Power Cord
- RS232 Cable
- Rackmount Hardware
- Owner's Manual



- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule Purchases

Specifications

OVERVIEW	
Users	2
PHYSICAL	
Unit Dimensions (hwd / in.)	1.7 x 17 x 10.6
Unit Dimensions (hwd / cm)	4.4 x 43.1 x 27
Unit Weight (lbs.)	5.1
Unit Weight (kg)	2.3
Color	Black
ENVIRONMENTAL	
Storage Temperature Range	-40 to 70 C / -40 to 158 F
Relative Humidity	80% Non-Condensing
Operating Temperature	0 to 40 C / 32 to 104 F
COMMUNICATIONS	
Port Control	Hotkeys, OSD
IP Remote Access	Yes
CONNECTIONS	
Ports	32
Computer/Server Ports	32
PC/Server Connections	VGA; USB; PS/2
Local Console Ports - Port 1	(x2) HD15 Female
Local Console Ports - Port 2	(x4) USB A Female
SPECIAL FEATURES	
Cat5 KVM Switch	Yes
CERTIFICATIONS	
NIAP-Certified Secure	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>