


## SmartRack 116 16-Port Console Cat5 KVM with 17-in. LCD

MODEL NUMBER: 0SU52091



### Description

#### Local Access

The SmartRack 116 comes with a 16 port Cat5 KVM switch. To access servers, just slide out the drawer and flip up its top to display the large, high resolution 17" TFT LCD display. The display is (VGA/SVGA/XGA/SXGA compatible) with front-panel high-quality controls and Touchpad for easy adjustment. It features triple layered security and plug-and-play installation.

#### Control More Servers

The SmartRack Cat5 KVM switches are compatible with all major operating systems and can control any server's brand and model, regardless of the server condition and network connectivity, covering the entire spectrum of crash scenarios. Use the KVM switch to control up to 16 servers in multiple platforms (PS/2, USB). The innovative ROC technology has each computer/ server directly connected to the switch via a ROC using standard CAT5 cable at a distance of up to 30m/100ft in a star configuration.

#### Slim, 1U Solution that Saves Space

The SmartRack Cat5 KVM switches are a single rail solution that occupies just 1U of rack space; it's the most efficient way to control your server rack.

### Features

- 16 Port KVM
- 17" TFT LCD Display
- BIOS level access
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Highlights

- 16 Port KVM
- 17" TFT LCD Display
- BIOS level access
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### System Requirements

#### Operating System

- Compatible with Windows, Linux, Unix and all other major operating systems

#### Resolution

- Supports video resolutions up to 1280 x 1024

#### Package Includes

- SmartRack 116 Cat5 KVM Switch
- RS232 Download Cable
- Rackmount Kit
- Owner's Manual



## Specifications

OVERVIEW	
Users	1
Console	Yes
PHYSICAL	
Unit Dimensions (hwd / in.)	1.7 x 17.6 x 25.2
Unit Dimensions (hwd / cm)	4.4 x 44.75 x 64
Unit Weight (lbs.)	40.1
Unit Weight (kg)	18.2
Color	Black
ENVIRONMENTAL	
Storage Temperature Range	-40 to 70 C / -40 to 158 F
Relative Humidity	10 to 90% RH
Operating Temperature	0 to 40 C / 32 to 104 F
COMMUNICATIONS	
Port Control	Hotkeys, OSD
IP Remote Access	No
CONNECTIONS	
Ports	16
PC/Server Connections	VGA; USB; PS/2
SPECIAL FEATURES	
Cat5 KVM Switch	Yes
CERTIFICATIONS	
NIAP-Certified Secure	No
WARRANTY	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	3-year limited warranty
-------------------------------------	-------------------------

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>