

2-Port DVI/USB KVM Switch w/ Audio and Cables

MODEL NUMBER: **B004-DUA2-K-R**



Description

The B004-DUA2-K-R is a 2-Port DVI/USB KVM Switch with audio and USB 2.0 peripheral sharing. It allows you to access, control, boot and reboot two computers from a single USB keyboard, USB mouse, and monitor. Switching between connected computers is quick and simple using keyboard hotkeys or pushbuttons. An independent audio/mic and USB peripheral switching function allows for an uninterrupted experience. A computer can be printing on a printer connected to one of the USB 2.0 peripheral ports, while you listen to audio from and access another computer; all at the same time.

The B004-DUA2-K-R uses DVI-I technology, allowing for the transmission of a digital (up to 1920 x 1200) or analog (up to 2048 x 1536) signal. A DVI to VGA adapter, such as Tripp Lite's P126-000, is required for conversion to an analog monitor. Whichever you use, full time DDC support provides the necessary EDID information required for optimal video performance on Windows 7 and other operating systems. Compatible with all major operating systems.

Features

- Fast, easy switching via keyboard hotkeys or pushbuttons
- Plug-and-play setup - no software required
- Hot-swap capability allows easy addition or removal of computers without powering down the switch or other computers
- Speaker and microphone connections allow for the sharing of audio components between systems
- Independent audio/mic and USB peripheral switching function allows for an uninterrupted experience. A computer can be printing on a printer connected to one of the USB 2.0 peripheral ports, while you listen to audio from and access another computer; all at the same time.
- Supports 2-Channel Stereo Audio
- Features two USB 2.0 ports for the sharing of USB peripherals (e.g. flash drives, printers, etc.) between the connected computers
- Uses DVI-I technology, allowing for the transmission of a digital (up to 1920 x 1200) or analog (up to 2048 x

Highlights

- Control 2 computers with a single DVI monitor, USB keyboard and USB mouse
- Switch ports via keyboard hotkeys or pushbuttons
- Allows for the sharing of audio components between systems; listen to music from one computer while accessing another
- Features two USB 2.0 ports for the sharing of USB peripherals between the connected computers
- (x2) 6ft USB cables and (x2) 6ft DVI + Audio KVM cable kits included
- Full time DDC support provides the necessary EDID information for optimal video performance on Windows 7 and other operating systems
- Compatible with all major operating systems

Applications

- Use this KVM switch when accessing two multimedia computers from a single USB keyboard, USB mouse, and monitor.

System Requirements

- KVM Console: A DVI monitor, USB keyboard, and USB mouse
- Computers: DVI-I port (P118-000 DVI-I to DVI-D Adapter is required for computers with DVI-D ports), and USB Port
- Audio (Optional): A microphone and speakers with 3.5mm Mini-Stereo connectors and a computer with 3.5mm Mini-Stereo ports



1536) signal. A DVI to VGA adapter, such as Tripp Lite's P126-000, is required for conversion to an analog monitor.

- To connect to a HDMI monitor, a DVI to HDMI adapter such as Tripp Lite's P132-000 is required (Audio is not supported when converting from DVI to HDMI).
- Full time DDC support provides the necessary EDID information for optimal video performance on Windows 7 and other operating systems
- Supports Microsoft® IntelliMouse® and the scrolling wheel on most mice
- (x2) 6ft USB cables and (x2) 6ft DVI + Audio KVM cable kits included
- Compatible with all major operating systems

- Compatible with all major operating systems

Package Includes

- B004-DUA2-K-R
- (x2) 6 ft. DVI-I + 3.5mm Audio Cable kits
- (x2) 6 ft. USB A-B Device Cables
- Owner's Manual
- External Power Supply (**Input:** 100-240V, 50/60Hz, 0.4A
Output: 5V, 2A)

Specifications

OVERVIEW	
Users	1
AC Adapter	Input: 100-240V, 50/60Hz, 0.4A Output: 5V, 2A
Max CPU	2
PHYSICAL	
Color	Silver
ENVIRONMENTAL	
BTUs	245.52
COMMUNICATIONS	
Port Control	Push Buttons, Hotkeys
IP Remote Access	No
CONNECTIONS	
Ports	2
PC/Server Connections	DVI; USB
Included KVM Cable (Equipment Side) - Connector 1	DVI-I (Male)
Included KVM Cable (Equipment Side) - Connector 2	(x2) 3.5mm (Male)
Included KVM Cable (Equipment Side) - Connector 3	USB A (Male)
Local Console Ports - Port 1	DVI-I (Female)
Local Console Ports - Port 2	(x2) USB A (Female)
Local Console Ports - Port 3	(x2) 3.5mm (Female)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

SPECIAL FEATURES	
Cat5 KVM Switch	No
CERTIFICATIONS	
Certifications	FCC, CE, RoHS Compliant
NIAP-Certified Secure	No
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>