

2x2 DVI over Cat5/Cat6 Matrix Splitter Switch, Video Transmitter

MODEL NUMBER: **B140-202**



Description

Tripp Lite's B140-202, 2X2 DVI Matrix Switch allows two DVI Single-Link video sources to be routed to one or two RJ45 outputs and extended up to 150-ft. @ 1920x1200 using Active (powered) Receiver, or up to 50-ft. @ 1920x1200 using Passive (non-powered) Rec. Switching between sources is done manually or with included remote control. Additional monitors can be added beyond the typical two by using Tripp Lite B140-110 daisy-chain Receivers - up to 4 monitors per channel. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Share two DVI video sources between two monitors
- Supports DVI Single Link computer resolutions up to 1920 x 1200 @ 60Hz
- Allows either input to be routed to either output, or the one input signal to both outputs
- Transmits over a single Cat5e/6 cable to a remote monitor up to 200-ft. away
- HDCP and EDID compliant
- Plug-and-Play
- A B140-Series remote receiver is needed at each monitor
- Active (powered) and Passive (non-powered) Receivers available
- Use 24AWG Solid Wire Cat5e/6 patch for maximum video performance
- Further expand the range and number of monitors with B140-110 Daisy-Chain Repeaters
- Compliant with the Federal Trade Agreements Act (TAA) for GSA schedule purchases

Highlights

- Share two DVI sources between two monitors
- Supports DVI Single Link computer resolutions up to 1920 x 1200 @ 60Hz
- Transmits over inexpensive Cat5e/6 cable up to 200 ft.
- Plug-and-Play
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- DVI video cards and DVI monitors

Package Includes

- B140-202 Local Transmitter Unit
- External Power Supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A
- Mounting Hardware
- Remote Control
- Owners Manual

Specifications

OVERVIEW

Display Style

Switch



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Type	DVI; UTP (Cat5, Cat5e, Cat6, Cat6a)
PHYSICAL	
Unit Dimensions (hwd / in.)	1.2 x 5.0 x 3.9
Unit Dimensions (hwd / cm)	3.05 x 12.7 x 9.91
Unit Weight (lbs.)	0.8
Unit Weight (kg)	0.36
Included Mounting Accessories	Yes
Color	Black
CONNECTIONS	
Connector A	DVI-I (FEMALE) (X2)
Connector B	RJ45 (FEMALE) (X2)
Ports	4
SPECIAL FEATURES	
Chromebook Compatible	No
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>