



Ring Terminal T&B Catalog Number:

REV717

UPC Number:

78621095871

Status:

Active

Description:

Insulated Vinyl Ring Terminal For Wire Range 6 AWG Stud Size 1/4, Blue
WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.

General

Insulation Type	Insulated Vinyl
Terminal Series	REV
Material	Copper
Finish	Electro -Tin Plated
Color	Blue
Wire Range	6
Stud Size	1/4

Dimension Information

Length (inches)	1.48
Width (inches)	.49
Maximum Insulation (inches)	.420
Stock Thickness	.04

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Available on Website
Application Tools	ERG4007, TBM6, TBM6S
Recommended Tool	ERG4007

Packaging

T&B Order Multiple	200
T&B Inner Pack	200
Package in Units	2000
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	6.25 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000192
Overview	Available on Website
Wire Guide Tables	Available on Website

Notes

Not available on Mylar Tape.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com