



**One-Piece
T&B Catalog Number:**

RSK301
78621087891
Active

**UPC Number:
Status:
Description:**

One-Piece Copper Grounding Connector for shielded and coaxial cables,
Shield Diameter 3.66 - 5.12, Yellow

Features

One-piece design connector for solderless, wrap-around crimping. Open shape to allow mid-span connections. Quick and easy to install: no heat or power required, no damage to the inner conductor. Transparent Polyester insulation for easy inspection. MIL specified (exceeds the performance requirements of MIL-F-21608) and industry approved technology, ideal for production in aircraft, aerospace and electronic industries where size and weight are of importance.

General

Insulation	Polyester film
Material	Copper, conform to CDA No. 110
Finish	Electro-Tin plated in accordance with MIL-T-10727A
Color	Yellow
Temperature Range	-85°C to +257°F

Dimension Information

Shield Diameter Range (inches)	.144 - .201
Shield Diameter Range (mm)	3.66 - 5.12
Ground Wire Size (AWG)	1 or 2 - 22 Str., or 1 - 20 Str.

Tooling

Installation Tools	ERG740
--------------------	--------

Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	7000
T&B Sold in UOM	Each
T&B Weight Per UOM	1.88 lbs. per 1000

Application Support

Overview	Available on Website
Installation Overview	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com