




Standard D-Sub



High-Density D-Sub

Best Seller



Item #	Description	1-9	10-24	25-99	100+
Slim-Line Gender Changer/Adapters - Reduce Port Receptacle Strain Up To 90%					
DGB9F	Slim-Line Gender Changer, DB9 Female/Female	4.95	4.46	3.96	CALL
DGB9M	Slim-Line Gender Changer, DB9 Male/Male	4.95	4.46	3.96	CALL
DGB15F	Slim-Line Gender Changer, DB15 Female/Female	5.95	5.36	4.76	CALL
DGB15M	Slim-Line Gender Changer, DB15 Male/Male	5.95	5.36	4.76	CALL
DGB25F	Slim-Line Gender Changer, DB25 Female/Female	6.95	6.25	5.56	CALL
DGB25M	Slim-Line Gender Changer, DB25 Male/Male	6.95	6.25	5.56	CALL
DGB37F	Slim-Line Gender Changer, DB37 Female/Female	8.95	8.05	7.16	CALL
DGB37M	Slim-Line Gender Changer, DB37 Male/Male	8.95	8.05	7.16	CALL
DGB50F	Slim-Line Gender Changer, DB50 Female/Female	10.95	9.86	8.76	CALL
DGB50M	Slim-Line Gender Changer, DB50 Male/Male	10.95	9.86	8.76	CALL

Socket Saver Adapters - Extend D-Sub Connector Usage and Avoid Major Repairs					
DGB9MF	Slim-Line Socket Saver, DB9 Male/Female	4.95	4.46	3.96	CALL
DGB15MF	Slim-Line Socket Saver, DB15 Male/Female	5.95	5.36	4.76	CALL
DGB25MF	Slim-Line Socket Saver, DB25 Male/Female	6.95	6.25	5.56	CALL
DGB37MF	Slim-Line Socket Saver, DB37 Male/Female	8.95	8.05	7.16	CALL
DGB50MF	Slim-Line Socket Saver, DB50 Male/Female	10.95	9.86	8.76	CALL

High-Density Slim-Line Gender Changers - Same Small Size for High-Density D-Subs					
DGBH15F	Slim-Line Gender Changer, HD15 Female/Female	7.95	7.16	6.36	CALL
DGBH15M	Slim-Line Gender Changer, HD15 Male/Male	7.95	7.16	6.36	CALL
DGBH26F	Slim-Line Gender Changer, HD26 Female/Female	10.55	9.50	8.44	CALL
DGBH26M	Slim-Line Gender Changer, HD26 Male/Male	10.55	9.50	8.44	CALL
DGBH44F	Slim-Line Gender Changer, HD44 Female/Female	11.71	10.54	9.37	CALL
DGBH44M	Slim-Line Gender Changer, HD44 Male/Male	11.71	10.54	9.37	CALL
DGBH62F	Slim-Line Gender Changer, HD62 Female/Female	15.23	13.71	12.18	CALL
DGBH62M	Slim-Line Gender Changer, HD62 Male/Male	15.23	13.71	12.18	CALL
DGBH78F	Slim-Line Gender Changer, HD78 Female/Female	16.43	14.79	13.14	CALL
DGBH78M	Slim-Line Gender Changer, HD78 Male/Male	16.43	14.79	13.14	CALL

High-Density Socket Saver Adapters - Great for Preventing Wear on High-Density Connectors					
DGBH15MF	Slim-Line Socket Saver, HD15 Male/Female	7.95	7.16	6.36	CALL
DGBH26MF	Slim-Line Socket Saver, HD26 Male/Female	10.55	9.50	8.44	CALL
DGBH44MF	Slim-Line Socket Saver, HD44 Male/Female	11.71	10.54	9.37	CALL
DGBH62MF	Slim-Line Socket Saver, HD62 Male/Female	15.23	13.71	12.18	CALL
DGBH78MF	Slim-Line Socket Saver, HD78 Male/Female	16.43	14.79	13.14	CALL

Slim-Line Gender Changer/Adapters - with Pin 9 Missing for Legacy VGA Cable Applications					
DGBV15F	Slim-Line Gender Changer, HD15 Female/Female	8.35	7.51	6.68	CALL
DGBV15M	Slim-Line Gender Changer, HD15 Male/Male	8.35	7.51	6.68	CALL
DGBV15MF	Slim-Line Socket Saver, HD15 Male/Female	8.35	7.51	6.68	CALL
DMA100MM	PS-2 Monitor Adapter, DB9 Male/HD15 Male	7.95	7.16	6.36	CALL

Slim-Line Gender Changers and Socket Saver - SCSI / Telco 50					
DGC50F	Slim-Line SCSI Gender Changer, 50 Pin Female/Female	13.29	12.23	11.16	CALL
DGC50M	Slim-Line SCSI Gender Changer, 50 Pin Male/Male	13.29	12.23	11.16	CALL
DGC50MF	Slim-Line SCSI Socket Saver, 50 Pin Male/Female	13.29	12.23	11.16	CALL

D-Sub Gender Changer Assortment Kit - Never Have a Mismatched Data Cable Again					
Each of these assortment kits have a total of 8 adapters for just about every D-Sub cable correction. DGB1010K includes: DB9, DB15, DB25 and DB37; the DGBH1010K high-density kit includes DGBH15, DGBH26, DGBH44 and DGBH62, each in male/male and female/female versions.					
DGB1010K	Slim-Line Gender Changer Kit, 8 Pieces	54.95	49.46	43.96	CALL
DGBH1010K	Hi-Density Gender Changer Kit, 8 Pieces	78.35	70.52	62.68	CALL

Slim-Line Block Ferrite Filter Adapters - Eliminate Problem EMI in Computing Devices					
L-com's plug-receptacle feed-thru adapter is a viable alternative solution for companies that need to rework (retrofit) existing designs in their effort to meet FCC regulations. Use these filtered D-Sub adapters where it's necessary to limit electromagnetic interference (EMI). Easy installation, economical cost, low profile and fully shielded. Four D-Sub sizes available, supplied with male/female hardware. Engineer's kit is also available and contains one of each adapter in a plastic carrying case.					
DGF9MF	Ferrite Filter (EMI) Adapter, DB9 Male/Female	8.35	7.68	7.01	CALL
DGF15MF	Ferrite Filter (EMI) Adapter, DB15 Male/Female	9.40	8.65	7.90	CALL
DGF25MF	Ferrite Filter (EMI) Adapter, DB25 Male/Female	10.45	9.61	8.78	CALL
DGF37MF	Ferrite Filter (EMI) Adapter, DB37 Male/Female	12.55	11.55	10.54	CALL
DGF100K	Engineer's Kit with 4 EMI Adapters	42.85	39.42	35.99	CALL

Easily panel mount adapters **Online Video**
L-com.com/Videos/A03

STEP 1

1. Remove standard hardware provided with adapter. Mount adapter from rear of panel.

STEP 2

2. Secure with jackscrew SDG450XS (purchased separately) from the front of the panel.

STEP 3

3. Thread hex nut SDHS (purchased separately) onto exposed threads of SDG450XS.

*** Note:** Maximum recommended panel thickness is 0.062" (0.2cm). Dimensions in excess of 0.062" (0.2cm) can limit proper cable mating due to hex nut protrusion. Panels exceeding 0.062" (0.2cm) can be milled down to the recommended thickness in the area around the adapter.