

Disconnects T&B Catalog Number:

TV18-250PD-XV

UPC Number:

72849414474

Status:


Active

Description:

Insulated Vinyl Piggy Back - 250 Series Disconnects for Wire Range 22-16, Red, Canister

Features

Male and Female Tabs Combined. Additional conductors may be added to existing installations without changing blocks. Molded Insulator. Brazed Seam. Internal Barrel Serrations. Funnel Entry.



General

Disconnect Type	Piggy Back - 250 Series
Insulation Type	Insulated Vinyl
Material	Brass with Copper Sleeve
Color	Red
Wire Range	22-16
Tab Size	.250 x .032

Dimension Information

W1 (inches)	.250
F1 (inches)	.323
B (inches)	.394
D (inches)	.157
F (inches)	.315
L (inches)	.886
T (inches)	.016
W (inches)	.260

Specifications

Temperature Rating	105°C
Voltage Rating	300V
Flammability Rating	UL 94 V-0

Tooling

Application Tools	WT112M, CM2000A
-------------------	-----------------

Packaging

T&B Order Multiple	900
T&B Inner Pack	75
Package in Units	900
Package Type	Canister
T&B Sold in UOM	Each
T&B Weight Per UOM	2.19 lbs. per 100
Alternate Package Qty	TV18250PDL

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125

T&B Technical Support
MS 3B-50
8155 T&B Blvd.

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289

