



Flag terminals allow a 90° connection to the terminal block without bending the wire.

Stock Thickness:

- AB = .03
- C = .04
- D = .06
- E = .06
- F = .07
- G = .08

Non-Insulated Flag

Cat. No.	Pkg. Qty.	Wire Range	Bolt Hole	Wt./Lbs. Per 1000	Dimensions			
					A	B	C	M
AB14-6A	100	22-14	#6	2½	.55	.31	.22	.39
AB51	1000	22-14	#6	2½	.55	.31	.22	.39
AB14-8A	100	22-14	#8	2½	.55	.31	.22	.39
AB52	1000	22-14	#8	2½	.55	.31	.22	.39
AB14-10A	100	22-14	#10	2½	.55	.31	.22	.39
AB53	1000	22-14	#10	2½	.55	.31	.22	.39
C51	1000	12-10	#6	5	.66	.31	.25	.48
C10-8A	50	12-10	#8	5	.66	.31	.25	.48
C52	500	12-10	#8	5	.66	.31	.25	.48
C10-10A	50	12-10	#10	5	.66	.31	.25	.48
C53	500	12-10	#10	5	.66	.31	.25	.48
D236	1000	9,8,7	#10	—	.83	.50	.25	.59
D226	1000	9,8,7	#10	—	.88	.50	.29	.64
D271	1000	9,8,7	¼"	—	.92	.50	.33	.68
E226	1000	6,5	#10	—	.93	.50	.29	.69
E271	1000	6,5	¼"	—	.97	.50	.33	.73
E272	1000	6,5	⅝"	—	1.05	.50	.41	.81
F226	1000	4,3	#10	—	1.07	.56	.33	.80
F271	1000	4,3	¼"	—	1.10	.63	.33	.80
F272	1000	4,3	⅝"	—	1.18	.63	.41	.88
F273	1000	4,3	⅜"	—	1.20	.63	.43	.90
G671	1000	2	¼"	—	1.20	.63	.33	.89
G672	1000	2	⅝"	—	1.28	.63	.41	.97
G673	1000	2	⅜"	—	1.32	.63	.46	1.02

U.L. Listed E9809

Installing tools: ERG-2004, WT129

Note: Not available on Mylar Tape.