



# Circus

Circus - now combining sleek styling and high-output illumination with a newly redesigned metal housing. The highly flexible, self-balancing shade allows the lamp head to be positioned horizontally, vertically and laterally. A fully enclosed, hands-free neck assembly not only makes the Circus simple to adjust, but also ideal for Industrial and Manufacturing environments as well as Cosmetology, Health Spas, Beauty Salons and Clean Room applications where optimal sanitation is sought.



- 2.5X greater light output than a traditional 22W T5 illuminated magnifier
- 6.5" diameter, optical-quality white-crown lens
- 3.5- (1.88X) or 5-diopter (2.50X) magnification
- Hands-free neck assembly - no knobs to tighten, nothing to adjust
- 3500 lux at focal length
- 22W T-5C fluorescent high-output lightsource virtually eliminates shadows
- Heavy-duty die-cast aluminum housing is non-corrosive and durable
- Fully-enclosed arm and neck assembly with protective rubber cover
- 45" covered spring-balanced arm with .75" steel tubing
- Removable tinted hinged lens cover
- High frequency electronic ballast
- Built-in handles enable easy positioning of lamp head
- 5 year warranty



## CODES

## CIRCUS MAGNIFIERS

---

Article Number	Light Source	Watt	Arm Length	Mount	Ctn.	Diopter	Colors
17980WT	T5 Fluorescent	22W	45.0/1143	Edge mount	1	3.5	<input type="checkbox"/>
17981WT	T5 Fluorescent	22W	45.0/1143	Edge mount	1	5	<input type="checkbox"/>