

TECHNICAL SPECIFICATION

Ref:	MLE116PB - Portrait	MLE116PW - Portrait	MLE116LB - Landscape	MLE116LW - Landscape
Description:	16W Wall Light with PIR	16W Wall Light with PIR	16W Wall Light with PIR	16W Wall Light with PIR
Fascia:	Matt black polycarbonate	Gloss white polycarbonate	Matt black polycarbonate	Gloss white polycarbonate
Backplate:	Matt black aluminium	Matt black aluminium	Matt black aluminium	Matt black aluminium
Lens:	Opal	Opal	Opal	Opal
Wattage:	16W	16W	16W	16W
Lumens generated:	550	550	430	430
Voltage:	230V	230V	230V	230V
LED array:	60 LEDs	60 LEDs	60 LEDs	60 LEDs
Power factor:	>0.9	>0.9	>0.9	>0.9
Colour temp:	ANSI 5700K	ANSI 5700K	ANSI 5700K	ANSI 5700K
Max. LED Life:	50,000 hrs	50,000 hrs	50,000 hrs	50,000 hrs
Efficiency:	<80%	<80%	<80%	<80%
Operating temp:	-32°C to +60°C	-32°C to +60°C	-32°C to +60°C	-32°C to +60°C
PIR range:	2-8m	2-8m	2-8m	2-8m
PIR angle	120°	120°	120°	120°
Activation time:	15secs - 4 mins	15secs - 4 mins	15secs - 4 mins	15secs - 4 mins
Dimensions (mm):	260(H) x 155(W) x 80(D)	260(H) x 155(W) x 80(D)	155(H) x 260(W) x 80(D)	155(H) x 260(W) x 80(D)
Weight (kg approx):	1kg	1kg	1kg	1kg
Warranty:	2 years	2 years	2 years	2 years