

## Soldering Tips, Nickel Plated, Packed on Card

For Soldering Iron	Type	Code No.	Description	Diameter mm	Width mm	Shelf Pack
SI15	S3	0054003499	straight, 3 pcs.	3,5	3,5	6
SI25	S1	0054003099	straight, 3 pcs.	4,5	4,5	6
	S2	0054003199	bent, 3 pcs.	4,5	4,5	6
SI40	S4	0054003299	bent, 3 pcs.	6,3	6,3	6
SI75	S8	0054003399	bent, 2 pcs.	9,5	9,5	6
SI100/SI120	S7	0054311099	bent, 1 pc.	12,5	12,5	6

## Soldering Tips, Nickel Plated, Packed in Polybag

For Soldering Iron	Type	Code No.	Description	Diameter mm	Width mm	Shelf Pack
SI15	43113	0054311399	straight	3,5	2,0	1
	43115	0054311599	straight	3,5	3,5	1
SI25	43003	0054300329	straight	4,5	4,5	1
	43004	0054300499	bent	4,5	4,5	1
SI40	43105	0054310500	straight	6,3	6,3	1
	43108	0054310899	bent	6,3	6,3	1
SI75	43106	0054310629	straight	9,5	9,5	1
	43109	0054310929	bent	9,5	9,5	1
SI100/SI120	43107	0054310799	straight	12,5	12,5	1
	43110	0054311000	bent	12,5	12,5	1
SI175	43111	0054311199	bent	16,0	16,0	1
SI251	43112	0054311299	bent	20,0	20,0	1

## Soldering Tips, Iron Plated "Longlife", Packed on Card

For Soldering Iron	Type	Code No.	Description	Diameter mm	Width mm	Shelf Pack
SI15	S31	0054321099	straight	3,5	0,4	6
	S32	0054321199	straight	3,5	2,0	6
SI25	S33	0054320099	straight	4,5	2,0	6
	S34	0054320199	straight	4,5	3,0	6
	S35	0054320299	straight	4,5	5,0	6
SI40	S36	0054322099	straight	6,3	5,0	6
	S37	0054322299	bent	6,3	5,0	6
SI75	S38	0054323099	straight	9,5	7,0	6
	S39	0054323299	bent	9,5	7,0	6
SI100/SI120	S41	0054324399	bent	12,5	12,5	6