

Product availability: Stock - Normally stocked in distribution facility

Price\*: 426.00 USD

### Main

Commercial Status	Commercialised
Product or component type	Definite Purpose Starter
[In] rated current	40 A
Motor power hp	7.5 hp 230 V AC 1 phase 3 hp 115 V AC 1 phase
[Ue] rated operational voltage	600 V AC
Control circuit voltage	208...240 V AC 60 Hz 220 V AC 50 Hz
Network number of phases	1 phase

### Complementary

Enclosure material	Painted sheet steel
NEMA degree of protection	NEMA 1
Locked rotor rated current	160 A 575 V AC 200 A 460 V AC 240 A 230 V AC
Poles description	2P
Range of product	DPS
Thermal overload type	Melting alloy
Number of thermal units required	1

### Ordering and shipping details

Category	21381 - 8911 DP
Discount Schedule	CP1
GTIN	00785901724766
Nbr. of units in pkg.	1
Package weight(Lbs)	5.83
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	CN

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will not be Compliant
REACH	Reference not containing SVHC above the threshold

### Contractual warranty

Period	18 months
--------	-----------