

Product data sheet

Characteristics

8911DPSO13V02

STARTER 600VAC 20AMP DPS +OPTIONS

Product availability: Stock - Normally stocked in distribution facility

Price*: 297.00 USD



Main

Commercial Status	Commercialised
Product or component type	Definite Purpose Starter
[In] rated current	20 A
Motor power hp	7.5 hp 575 V AC 3 phases 7.5 hp 460 V AC 3 phases 1.5 hp 115 V AC 1 phase 7.5 hp 230 V AC 3 phases 3 hp 230 V AC 1 phase
[Ue] rated operational voltage	600 V AC
Control circuit voltage	120 V AC 60 Hz 110 V AC 50 Hz
Network number of phases	3 phases

Complementary

NEMA degree of protection	Not rated (open device)
Locked rotor rated current	80 A 575 V AC 100 A 460 V AC 120 A 230 V AC
Poles description	3P
Range of product	DPS
Thermal overload type	Melting alloy
Number of thermal units required	3

Ordering and shipping details

Category	21381 - 8911 DP
Discount Schedule	CP1
GTIN	00785901116752
Nbr. of units in pkg.	1
Package weight(Lbs)	2.44
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	CN

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will not be Compliant
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Period	18 months
--------	-----------