



**Technical Characteristics**

Operating Torque/Force	4 Pounds
Actuator	Push Rod
Actuation	Horizontal
Actuator Action	Spring Return
Total Travel	0.25 Inches
Differential Travel	0.03 Inches
Body Material	Zinc Alloy
Pre-Travel	0.08 Inches
Approvals	UL Listed File Number E42259 CCN NKCR - CSA Certified File Number LR25490 Class 3211-03 - CE Marked
Body Type	Standard Plug-In
Catalog Reference Number	9006CT0101
Connection Type	Conduit Entrance (0.5 Inch NPT)
Wire Size	#12 to #22 AWG
Contact Configuration	1 N.O./1 N.C.
Contact Rating	NEMA A600/Q600
Contact Material	Silver Alloy
Contact Operation	Snap Action
Maximum Voltage Rating	600V
Ampere Rating	10A
Contact Form	Form Z - SPDT-DB
Terminal Type	Screw Clamp
Mounting Type	Front/Rear
Enclosure Rating	NEMA 1/2/4/6/6P/12/13
Head Type	Side Plunger
Pilot Light	None
Type of Duty	Heavy Duty
Operating Temperature Range	0 to 185 Degrees F
Type	C

**Shipping and Ordering**

Category	21499 - Limit Switches, Heavy Duty, Type C
Discount Schedule	CP1

Generated: 05/28/2009 10:42:24

Article Number	785901500704
Package Quantity	1
Weight	1.18 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.