



620 Amps 600 Volts AC/DC

Wire Range

- Line: (2) 350 kcmil - #4
- Load: (2) 350 kcmil - #4

Electrical Ratings

- 620 Amps
- 600V per UL 1059 & CSA 22.2 No.158, class B & C requirements
- Short circuit current ratings (SCCR): See SCCR section below for specifications.
- CU7AL - 75°C connector terminal rating with copper or aluminum wire
- Factory & Field Wiring


Agency Compliance

- UR - UL Recognized Terminal Block, Evaluated to UL 1059, File No.XCFR2.E62806
- CSA - certified to C22.2 No. 158, File No. LR19766 (wire classes B & C only)
- CE compliant to IEC 60947-7-1

Material Information

- Insulator base:
 - Phenolic
 - Flammability rating of insulator base UL94V0
 - Insulator base temperature rating: -40°C to 150°C (UL RTI)
- Connector: aluminum, tin plated
- Terminal set screws: aluminum, tin plated
- Connector mounting screws: steel, zinc plated
- RoHS compliant

Termination Specifications

Line & Load Side	Wire Size (CU Stranded)	Torque	Wires / Terminal	Wire Class (UL) ¹
	350 - 300 kcmil	31.1 N·m (275 lbf·in)	1	B, C
	250 - 2	31.1 N·m (275 lbf·in)	1	B, C, G, H, I (DLO)
	4	31.1 N·m (275 lbf·in)	1	B, C

- Aluminum wire range: 350 kcmil - #4 AWG
- Wire strip length: 1 1/16in. (27mm)
- Terminal screw drive: 5/16 in. hex

¹ For information on copper stranded wire classes please reference:
<http://www.marathonsp.com/CatalogPDFs/Flexible-Stranded-Wire.pdf>

Short Circuit Current Ratings (SCCR)

- The suitable conductor ranges are limited to the table values only for achieving the SCCR in excess of the default rating of 10,000A.
- Other conductor combinations within the "Terminal Specifications" noted are suitable for achieving a SCCR of 10,000A (the default rating of terminal blocks).
- Enclosure size – Investigated with a minimum 16x12x6 enclosure. Use in smaller enclosures is subject to end use evaluation.

SCCR With Fuses

Wire Class	Suitable Conductors		Max Overcurrent Protection Fuse Required Amp Rating / Class						SCCR RMS Sym. Amps 600V. Max
	Line	Load	J	T	RK1	RK5	G	CC	
B, C	350 - 4	350 - 4	600	600	-	-	-	-	50,000
B, C	350 - 4	350 - 4	450	450	400	200	60	30	100,000
G, H, I	250 - 2	250 - 2	600	600	-	-	-	-	50,000
G, H, I	250 - 2	250 - 2	450	450	400	200	60	30	100,000
(*)	350 - 4	350 - 4	None						10,000

* Any wire class evaluated (see terminal specification section)

Installation & Accessories

- Mounting (Panel):
 - For use with 1/4 fastener.
 - Torque mounting fastener to 30-40 lbf-in (3.4 - 4.5 N·m).
- Covers:
 - Flat covers available upon request
 - Catalog Number: CH145x (replace "x" with number of poles)
 - Covers are clear polycarbonate
 - Accessory covers are not intended to provide insulation for electrical spacings.
- Marker Strip: white vinyl strip with mounting screws available.
- Printing options available, consult customer service for specifications.

Drawing

