

6EP1311-1SH12

Stabilized power supply DC 5 V / 6.3 A

Specified for operation on single-phase AC systems

Nominal input voltage AC 100-240 V, wide-range

Input voltage range AC 85 to 264 V

Efficiency for nominal values, typ. 83 %

Nominal output voltage DC 5 V, adjustable range 4.6 to 5.4 V

Total tolerance +/- 3 %, residual ripple < 100 mVss

Nominal output current 6.3 A

Ambient temperature -20 to 55°C

Protection class I, degree of protection IP20,

isolation SELV to EN 60950 and EN 50178

RFI specification class B to EN 55022

Certificated to CE, UL/cUL FM

Shipbuilding approval GL