


### 136 LUMEN G9 LED LAMP

Ideal replacement for halogen G9 in wall lights, multi lamp ceiling lights and many other applications

- Ultra low power consumption: fantastic energy saving
- 136 lumen output: for excellent background lighting level
- 2700K colour temperature: for warm, close to halogen, colour appearance
- 20,000 hours average life expectancy: much reduced lamp replacement cycle & maintenance
- Similar dimensions to halogen G9: allows retrofit into many compact fittings
- Not for use in enclosed fittings

• M.O.M: 10 / O.P.Q: 10

**2 YEAR WARRANTY**



Code	Wattage	Cap Type	Colour Temp.	Lumens	Beam Angle	Avg. Rated Life (Hrs)	Energy Rating
G9WW136	2.2W	G9	2700K	136 lm	300°	20,000 hrs	A+



#### LAMP SPECIFICATIONS:

Nominal luminous flux	<b>136 lm</b>
Rated Wattage	2.2W
Rated luminous flux	136 lm
Nominal life time of the lamp	20,000 hrs
Colour temperature	2700K
Number of switching cycles before premature lamp failure	>10,000
Warm-up time up to 60 % of the full light output	Instant full light
Dimmable	No
Lamp dimensions (L/Ø)	48 x 14mm
Nominal beam angle	300°
Rated power	2.2W
Rated lamp lifetime	20,000 hrs
Lamp power factor	>0.5
Lumen maintenance factor at end of nominal life	70%
Starting time	<0.5s
Colour rendering	>80
Colour consistency	Within 6 step Macadam ellipse
Rated beam angle	300°
Cap type	G9