

# Han MegaBit Single Entry, M + shield



Part number:	09 14 008 3022
Description:	Han MegaBit Single Entry, M + shield
<b>Features</b>	
Combination of contacts:	2 x 4 + shielding
Gender:	male
Rated current:	10 A
Series:	Han-Modular®
Limiting temperature, min.:	-40 °C
Limiting temperature, max.:	85 °C
Termination method:	Crimp terminal
Hint:	Please order crimp contacts separately. Please order the adapter module separately.
<b>Connection data</b>	
Contact resistance:	<= 4 mOhm
Contact info:	with additional shield connection to the hinged frame
Rated current:	10 A
Rated voltage:	50 V
Rated impulse voltage:	0.8 kV
Pollution degree:	3
Cable diameter, min.:	5 mm
Cable diameter, max.:	12 mm
<b>Material properties</b>	
Material, insert:	polycarbonate
Surface, outer conductor:	nickel plated contacts
Material, outer conductor:	zinc alloy

<b>Dimensions and weight</b>	
Net Weight:	44.6 g
<b>Version</b>	
Type of module:	Han® MegaBit Insert
<b>Norms and specifications</b>	
Flammability insert acc. to UL 94:	V 0
Specification:	IEC 60664-1 IEC 61984