


G-6 SINGLE CONTACT BAYONET BASE

MINIATURE LAMP

28V .230A

WAMCO PART NO.		ENVELOPE SIZE		BASE TYPE	RATING		FILAMENT SHAPE	
WL-1251		G-6		BA15s	28V .230A		2C-26	
TEST VOLTS	CURRENT (A)			LIGHT OUTPUT (MSCP)			LIFE HRS	
	MIN	NOM	MAX	MIN	NOM	MAX		
28V	.207	.230	.253	2.25	3.0	3.75	2,000	

DIMENSIONAL CHARACTERISTICS



NOTES

1. LCL = .75"
2. Nickel-plated brass construction base
3. Part mark WL-1251
4. RoHS compliant
5. ANSI trade number 1251

