


# G-6 DOUBLE CONTACT BAYONET BASE

## MINIATURE LAMP

28V .230A

WAMCO PART NO.		ENVELOPE SIZE	BASE TYPE	RATING	FILAMENT SHAPE		
WL-1252		G-6	BA15d	28V .230A	2C-26		
TEST VOLTS	CURRENT (A)			LIGHT OUTPUT (MSCP)			LIFE HRS
	MIN	NOM	MAX	MIN	NOM	MAX	
28V	.207	.230	.253	2.25	3.0	3.75	2,000

## DIMENSIONAL CHARACTERISTICS



## NOTES

1. LCL = .75"
2. Nickel-plated brass construction base
3. Part mark WL-1252
4. RoHS compliant
5. ANSI trade number 1252

