


Lamp Specification

Wamco Part No.	Envelope Size	Base Type	Rating	Filament Shape
WL-1308	B-6	BA15s	28V .56A	CC-8

Test Volts	Current (A)			Light Output (MSCP)			Life Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
28	.504	.560	.616	12.8	16	19.2	2,000 Hrs

Dimensional Characteristics:

1. L.C.L. = 1.06" (26.9mm)
2. Base = Nickel-plated Brass Construction.
3. Spiral Filament Supports.



Title:

**B-6 Single Contact Bayonet Base Lamp
28V .560A Gas-Filled**

Drawn	7/19/00	CI	Notes: Unless otherwise specified, all dimensions are in inches.
Checked	7/19/00	EB	
Approved	7/19/00	EB	