


T-3¼ MINIATURE BAYONET BASE

MINIATURE LAMP

13V .33A

WAMCO PART NO.		ENVELOPE SIZE		BASE TYPE		RATING		FILAMENT SHAPE	
WL-1816		T-3¼		BA9s		13V .33A		C-2V	
TEST VOLTS	CURRENT (A)			LIGHT OUTPUT (MSCP)			LIFE HRS		
	MIN	NOM	MAX	MIN	NOM	MAX			
13V	.297	.330	.363	2.25	3.00	3.75	1,000		

DIMENSIONAL CHARACTERISTICS



NOTES

1. LCL = .63" (16mm)
2. Nickel-plated brass construction base
3. Part mark WL-1816
4. RoHS compliant
5. ANSI trade number 1816

