

T-1³/₄ BI-PIN BASE


SUBMINIATURE LAMP

28V 40mA

WAMCO PART NO.	ENVELOPE SIZE	BASE TYPE	RATING	FILAMENT SHAPE
WL-7387	T-1 ³ / ₄	BP	28V 40mA	C-2F

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (MSCP)			LIFE HRS
	MIN	NOM	MAX	MIN	NOM	MAX	
28V	36.0	40.0	44.0	.225	.300	.375	7,000

DIMENSIONAL CHARACTERISTICS



NOTES

1. Part mark WL-7387
2. RoHS compliant
3. ANSI trade number 7387

