


G-6 SINGLE CONTACT BAYONET BASE

MINIATURE LAMP

6.5V 1.02A

WAMCO PART NO.	ENVELOPE SIZE	BASE TYPE	RATING	FILAMENT SHAPE			
WL-81	G-6	BA15s	6.5V 1.02A	C-2R			
TEST VOLTS	CURRENT (A)			LIGHT OUTPUT (MSCP)			LIFE HRS
6.5V	MIN	NOM	MAX	MIN	NOM	MAX	500
	.918	1.020	1.12	4.5	6.0	7.5	

DIMENSIONAL CHARACTERISTICS



NOTES

1. LCL = .75"
2. Nickel-plated brass construction base
3. Part mark WL-81
4. RoHS compliant
5. ANSI trade number 81

