

4mm Digital Multimeter Probe **TENMA™**

**RoHS
Compliant**



Descriptions:

This Digital multimeter probe set combines the versatility of 2mm (0.08") diameter smooth tips and 4mm banana plug tips into one probe set. Set comes as a pair Black and Red probe bodies together.

Features:

- Standard size probe bodies
- Black and Red pair
- IC tip covers included (banana plug contacts) grey

Specifications:

IEC Rating	: 1,000 V CAT II
Current	: 36A (Max.)
Tip	: Brass, Nickel plated
Contact	: (Banana Plug) BeCu, Nickel plated
Temperature	: -20°C to +80°C

Part Number Table

Description	Part Number
Pair, Black & Red Probe Bodies with Replaceable Tips Probe Bodies	76-080

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.