



**NetShelter SX 42U 600mm Wide x 1070mm Deep
Enclosure with Sides Black**
Part Number: AR3100



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Options](#) [Ratings and Reviews](#)

Physical

Net Weight	275.20 lbs. (125.09 kg)
Maximum Height	78.39 inches (1991 mm)
Maximum Width	23.62 inches (600 mm)
Maximum Depth	42.13 inches (1070 mm)
Shipping Weight	318.00 lbs. (144.55 kg)
Shipping Height	83.40 inches (2118 mm)
Shipping Width	29.62 inches (752 mm)
Shipping Depth	48.00 inches (1219 mm)
Weight Capacity (static load)	3000.00 lbs. (1363.64 kg)
Weight Capacity (dynamic load)	2250.00 lbs. (1022.73 kg)
Minimum Mounting Depth	7.52 inches (191 mm)
Maximum Mounting Depth	36.02 inches (915 mm)
Rack Height	42U
Rack Width	19"
Color	Black
Units per Pallet	1.00
Vertical Posts	16 gauge
Front Door	16 gauge
Rear Door	18 gauge
Roof	18 gauge
EIA Mounting Rails	14 gauge
Side Panels	18 gauge

Conformance

Approvals	UL 2416, UL 60950-1
Standard warranty	5 year repair or replace
Standards	EIA-310-E

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
PEP	Available in Documentation tab
EOLI	Available in Documentation tab
Other Environmental Compliance	China RoHS

*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.