

# DYN-630



Product type	IP camera
Operation system	Embedded operating system
<b>Web environment</b>	
Web protocol	TCP/IP, UDP/IP, HTTP, SMTP, FTP, DHCP, DDNS, UPNP, NTP, RTSP, ONVIF
LAN port	10Base-T/100Base-TX
Wifi	WIFI, 802.11 b/g/n
<b>Image performance</b>	
Resolution	720P, 640*360, 320*180
Compression mode	H.264/M-JPEG
Max frame rate	30fps
<b>Other parameters</b>	
Lens	f=3.6mm, F=2.0
Min. illumination	IR on, 0 Lux
Electronic shutter	1/50s(1/60s)-1/100,000 s
SNR	48db
Safety performance	Three levels of user rights
Install mode	Wall-mounted / ceiling-mounted
Other performance	PC software, support for Microsoft Windows 98/2000/XP/Vista/Windows 7/Mac OS, And the Internet Explorer6.1 and above version or browser compatibility, Firefox, etc., provide iSmartViewPro client software
Power supply	DC 5V
Sensor	CMOS Sensor
IP camera performance	Support video control, Two-way voice talkback, motion detection, external alarm(sends information to alarm the server by Email, FTP); Manufacturers provide free DDNS, and has been written into equipment; 11pcs IR LEDs,8 meters effectively; Platform level angle 340°, 110°vertical angle; automatically control through the photoresistor;
Audio input	With microphone
Audio output	Provide the audio output interface
Alarm in	None
Alarm out	None
Power consumption	Power<6W
<b>Appearance parameters</b>	
Body size	111*106*124mm
Product weight	0.27kg
<b>Environment parameters</b>	
Environment temperature	-10°C--50°C
Environment humidity	below 85% RH