



Philips LED
Candle

3 W (25 W)
E14 cap
Warm white



8718291786955



Add a beautiful sparkle to your home

Sparkling light for a warm and inviting atmosphere

Philips LED clear candles provide a beautiful, sparkling light effect and an exceptionally long life. Beautiful both switched on and switched off, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

Instant brightness

- Instant light when switched on

Sustainable choice

- Lasts up to 15 years
- Very low energy consumption; saving at least 80%

Warm sparkling light

- True incandescent-like warm white light (2700 K)
- High colour rendering (CRI > 80) for vivid colours

Innovative optical design

- Special optical design creating sparkling light effect

PHILIPS

Candle
3 W (25 W) E14 cap, Warm white

Highlights

Warm white light (2700 K)

Light can have different colour temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, cosier light, while those with a higher Kelvin value produce a cool, more energising light.

Instant light when switched on



No need to wait: Philips LED light bulbs provide their full level of brightness immediately upon switching on.

High colour rendering (CRI>80)



The colour rendering index (CRI) is used to describe the effect of a light source on colour appearance. Natural outdoor light has a CRI of 100 and is used as the standard of comparison for any other light source. The CRI of Philips LED light bulbs is always higher than 80, close to the sun's value, reflecting colours truly and naturally.

Very low energy consumption



By replacing traditional light bulbs with a Philips LED alternative, you will gain immediate, significant energy savings while contributing to a sustainable planet.

Lasts up to 15 years



With a lifetime of up to 15,000 hours, this Philips LED bulb will ensure your desired atmosphere for up to 15 years.*

Special optical design



With its clear, elegant design and innovative LED technology, this decorative bulb produces a warm, sparkling light effect, adding a cosy quality to your home atmosphere.

8718291786955

Specifications

Bulb characteristics

- Shape: Candle
- Cap/fitting: E14
- Voltage: 220-240 V
- Dimmable: No

Power consumption

- Wattage: 3 W
- Wattage equivalent: 25 W
- Energy efficiency label: A+
- Power consumption per 1000h: 3 kW h

Light characteristics

- Light output: 250 lumen
- Colour: Warm White
- Colour temperature: 2700 K
- Light effect/finish: Warm White
- Starting time: < 0.5 s
- Warm-up time to 60% light: Instant full light
- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80

Durability

- Number of switch cycles: 50,000
- Lumen maintenance factor: 0.7
- Average life (at 3 hrs/day): 15 year(s)

Bulb dimensions

- Height: 113 mm
- Width: 39 mm

Other characteristics

- Mercury content: 0 mg
- Power factor: 0.5
- Lamp current: 35 mA

Rated values

- Rated power: 3.0 W
- Rated luminous flux: 250 lm
- Rated lifetime: 15,000 hour(s)



Issue date 2015-01-20

Version: 2.0.1

12 NC: 9290 011 14601

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* **Based on average usage of 3 hours per day