


TE CONNECTIVITY (TE)

-

MULTICORE CABLE



TE CONNECTIVITY (TE)

44AM1111-22-9-9CS2275

- 44AM1111-22-9-9CS2275
- TE Internal Number: 146439-000
- Mil-Spec: M27500-22ML1T08
- Alias ID: 4-1191058-8

Converted to EU RoHS/ELV Compliant

- Cable Type **Spec 44**
- Conductor Diameter **.79 mm [.031 in]**
- Number of Strands **19**
- Strand Size (AWG) (AWG) **34**
- Overall Outside Diameter **2.01 mm [.079 in]**

Product Type Features

- Cable Type **Spec 44**
- Shielded **Yes**
- Cable Style **Jacketed, Round Braided**
- Product Type **Cable**
- Product Classification **Cable - High Performance - Spec 44, 55 & RCW**

Configuration Features

- Number of Strands **19**
- Number of Conductors **1**

Electrical Characteristics

- Voltage Rating (V) **600**

Body Features

- Shield Material **Copper**
- Shield Diameter **1.65 mm [.065 in]**
- Jacket Color **White**
- Wire Color **White**
- Conductor Material **Tin-Plated Copper**

Dimensions

- Conductor Diameter **.79 mm [.031 in]**
- Strand Size (AWG) (AWG) **34**
- Overall Outside Diameter **2.01 mm [.079 in]**
- Wire Size (AWG) (AWG) **22**
- Wire Size (mm²) (mm²) **.3255**
- Wire Diameter **1.19 mm [.047 in]**

Usage Conditions

- Operating Temperature Range (°C) **-65 – 150**