

Product data sheet

Characteristics

GV2MC01

TeSys GV2 - Enclosure for TeSys GV2ME - IP41

Product availability: Stock - Normally stocked in distribution facility

Price*: 54.00 USD



Main

Commercial Status	Commercialised
Range of product	TeSys GV2
Product or component type	Enclosure
Device short name	GV2MC
Accessory / separate part category	Mounting accessory
Product compatibility	GV2ME
Dedicated enclosure type	Surface mounting

Complementary

Auxiliary mounting location	Left Right
Height	5.79 in (147 mm)
Width	3.66 in (93 mm)
Depth	3.31 in (84 mm)
Product weight	0.64 lb(US) (0.29 kg)

Environment

IP degree of protection	IP41
-------------------------	------

Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	00785901882725
Nbr. of units in pkg.	1
Package weight(Lbs)	0.60
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	CZ

Contractual warranty

Period	18 months
--------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative