

PRODUCT SPECIFICATION

Brand	Kasp
Product Range	Disk padlocks
Catalogue number	160
Date	04/02/2010

Range Description


Disc Padlocks

Features

- Hardened steel shackle – extra protection against hacksaw and cropping attacks
- Double bolted locking mechanism – extra strength to resist torsion and pull attacks
- Stainless steel body – maximum resistance to corrosion
- 5 Pin cylinder with anti pick mushroom pins (4 pin on 60mm) – extra protection against picking
- Paracentric keyway extra protection against manipulation
- Drill resistant keyway (70mm only) – protects the cylinder from drill attack

These padlocks are supplied display packed in sealed blisters and individually boxed

2 keys are supplied with each lock



Technical product information

Body – Stainless steel

Shackle- Hardened alloy steel, chrome plated

Locking mechanism:

60mm - Pin tumbler cylinder type, 4 pin cylinder, Brass pins – Top pin 4 is plain, top pins 1 to 3 are mushroom type.

70mm - Pin tumbler cylinder type, 5 pin cylinder, Brass pins – Top pin 5 is plain, top pins 1 to 4 are mushroom type.

Key differs:

60mm - 250

70mm - 2500

Re-keyable – No

Security rating:

Item	Security rating
K16060	9
K16060D	9
K16070	11
K16070D	11
K16070A1	11
K16070A2	11
K16070A2	11

Shackle Dimensions:

Dimensions mm	Shackle		
	Dia	Internal width	Internal height
K16060	8	15	13
K16060D	8	15	13
K16070	10	19	17
K16070D	10	19	17
K16070A1	10	19	17
K16070A2	10	19	17
K16070A2	10	19	17

Use environment- Normal outdoor use

Recommended applications- The disk lock is an extremely popular padlock suitable for a wide range of applications where a high level of security is required, it is recommended that the lock is used in conjunction with the 260 series hasp and staple

Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	These products do not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	KASP Disk padlocks are guaranteed against defects in manufacture and/or materials for 10 years Damage caused through inappropriate use or attempted break in is not covered
Country of origin	China

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K16070D260	-	-	-	-	175	35	160	610