

# PRODUCT SPECIFICATION

**Carl  
Kammerling**  
International

<b>Brand</b>	Kasp
<b>Product Range</b>	Dial combination padlock
<b>Catalogue number</b>	115
<b>Date</b>	08/09/2010


## Range Description

Dial combination padlock

## Features

- Hardened steel shackle – extra protection against hacksaw and cropping attacks
- 40 digit mechanism offers over 60,000 combinations for added security
- 3 Digit factory pre set code

Supplied display packed in sealed blisters



Technical product information	<p><b>Body</b> – Steel, chrome plated</p> <p><b>Shackle</b>- Hardened steel, chrome plated</p> <p><b>Security rating:</b></p> <table border="1"> <tr> <th>Item</th> <th>Security rating</th> </tr> <tr> <td>K11548</td> <td>4</td> </tr> </table> <p><b>Shackle Dimensions:</b></p> <table border="1"> <thead> <tr> <th rowspan="2">Dimensions mm</th> <th colspan="3">Shackle</th> </tr> <tr> <th>Dia</th> <th>Internal width</th> <th>Internal height</th> </tr> </thead> <tbody> <tr> <td>K11548</td> <td>7</td> <td>20</td> <td>18</td> </tr> </tbody> </table> <p><b>Use environment</b>- Light outdoor use</p> <p><b>Recommended applications</b>- Ideal for keyless locking of lockers, cupboards, sheds, gates etc.</p>	Item	Security rating	K11548	4	Dimensions mm	Shackle			Dia	Internal width	Internal height	K11548	7	20	18
Item	Security rating															
K11548	4															
Dimensions mm	Shackle															
	Dia	Internal width	Internal height													
K11548	7	20	18													
Standards compliance	None applicable															
User health and safety information	None applicable															
RoHS/WEEE compliance	This product does not fall within the scope of RoHS or WEEE regulations															
Material safety data	None applicable															
Warranty	KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years Damage caused through inappropriate use or attempted break in is not covered															
Country of origin	China															

## Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K11548D	48	34	72	148	110	40	170	169