

You are here:

[Home](#) > [Products](#) > [Replacement Batteries](#)



**APC Replacement Battery Cartridge #43**  
Part Number: RBC43



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Ratings and Reviews](#)

**Batteries & Runtime**

Battery Volt-Amp-Hour Capacity  
480

Battery Type  
Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof

Battery mounting  
Enclosed battery cartridge

Expected Battery Life (years)  
3 - 5

RBC™ Quantity  
1

**Physical**

Net Weight  
42.00 lbs. (19.09 kg)

Maximum Height  
3.00 inches (76 mm)

Maximum Width  
8.50 inches (216 mm)

Maximum Depth  
21.00 inches (533 mm)

Shipping Weight  
45.00 lbs. (20.45 kg)

Shipping Width  
15.50 inches (394 mm)

Shipping Height  
9.00 inches (229 mm)

Shipping Depth  
30.25 inches (768 mm)

Units per Pallet  
12.00

**Environmental**

Operating Environment  
32 - 104 °F (0 - 40 °C)

Operating Relative Humidity  
0 - 95%

Operating Elevation  
0-10000 feet (0-3000 meters)

Storage Temperature  
5 - 113 °F (-15 - 45 °C)

Storage Relative Humidity 0 - 95%
Storage Elevation 0-50000 feet (0-15000 meters)
<b>Conformance</b>
Standard Warranty 1 year repair or replace, 30 days (Japan only)
<b>Sustainable Offer Status</b>
RoHS Compliant
REACH REACH: Contains No SVHCs
PEP Available in Documentation tab
EOLI Available in Documentation tab

\*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.