

## Hand Wind Reels

Hand wind reels are designed for heavy duty industrial storage applications. Perfect for storing extension cords, or continuous power service.

### HW100 HAND WIND REEL

- Heavy duty design for storage of extension cords, power cables, rope or hoses
- Center cavity access to the end of conductor

### HW200 HAND WIND REEL

- 15 Amp duplex receptacle on reel and plug on free end of cable
- Point of use
- Disconnecting electrical device is required to wind or unwind cable

### HW300 HAND WIND REEL

- Equipped with slip ring, power cable, and plug
- Payout cable has receptacle
- Ideal for continuous service


Maximum capacity- all models

- 3 cond. #16 AWG SO (.430 in. dia.) 200 Ft.
- 3 cond. #14 AWG SO (.560 in. dia.) 125 ft.
- 3 cond. #12 AWG SO (.640 in. dia.) 100 ft.
- usable spool vol. 500 cu. in.



3 cond. Type SO Cable Size	length ft.	m	Amperage cord off reel	Series-UL listed/CSA certified		
				HW100	HW200	HW300
#16 AWG	50	15.24	10	HW122	HW222	HW322
#16 AWG	100	30.48	10	HW124	HW224	HW324
#14 AWG	50	15.24	15	HW132	HW232	HW332
#14 AWG	100	30.48	15	HW134	HW234	HW334
#12 AWG	50	15.24	15	HW142	HW242	HW342
#12 AWG	100	30.48	15	HW144	HW244	HW344
Cable Not Supplied			15	HW100	HW200	HW300

All rated at 125 volts.



HW200 Series Shown



HW100



HW200



HW300

