



### Main

Ampere Rating	60A
Depth	4.34 Inches
Height	7.31 Inches
Maximum Voltage Rating	600V
Mounting Type	Door
NEMA Size	2
Terminal Type	Pressure Wire
Type	D10
Width	5.88 Inches

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.