



Description

- Ideal shelf liner matting; flexible, tough, and fairly hard
- Low cost
- Made of a modified homogeneous polyethylene; offers excellent chemical resistance
- Should not be used at solder stations

Specifications

Rp-p: 1×10^3 to $< 1 \times 10^6$ ohms, tested per IEC 61340-2-3, meets EN 61340-5-1

Rg: 1×10^3 to $< 1 \times 10^6$ ohms, tested per IEC 61340-2-3, meets EN 61340-5-1


Thickness: 1.5mm

Weight: 1.4 kg/m²

Colour: black

Item	Description
VER-27088	EVA Mat 1.5mm x 1.1m x 3.3m, No Studs

"All working surfaces and storage racks on which unprotected ESDS [ESD sensitive items] may be placed shall be capable of being connected to EPA ground and shall have a point-to-point resistance and resistance to EPA ground in accordance with table 1 (Rp greater or equal to 1×10^4 , less than or equal to 1×10^9 ohms, and Rg greater or equal to 7.5×10^5 to less than or equal to 1×10^9 ohms) and shall contain a groundable point."



Made in the United Kingdom

*Colour and texture may vary between lots and mills

Vermason

EVA Bench Matting and Shelf Lining

VERMASON LTD.
UNIT C, 4TH DIMENSION, FOURTH AVENUE, LETCHWORTH,
HERTS, SG6 2TD UK
PHONE: +44 (0) 1462-672005, FAX: +44 (0) 1462-670440
E-MAIL:Service@Vermason.co.uk, INTERNET: Vermason.co.uk

Drawing Number
VER-27088

DATE:
October 2015