



Technical Characteristics

Catalog Reference Number	9034CT9701
Action	Standard
Application	Primarily used on condensation pumps
Contact Arrangement	DPST
Float Movement	4.75 to 9.25 Inches
Float Position	Left
Enclosure Type	General Purpose (Indoor)
Enclosure Rating	NEMA 1
Material	Float/Rod: Stainless Steel - Quad Ring Seal: Buna N
Mounting Type	Flange
Horsepower Rating (3-Phase)	3HP@115VAC - 5HP@230VAC - 1HP@460/575VAC
Maximum Voltage Rating	575VAC
Terminal Type	Screw Clamp
Type	C
Horsepower Rating (1-Phase)	2HP@115VAC - 3HP@230VAC
Number of Poles	2-Pole

Shipping and Ordering

Category	21601 - Switches, Float, Commercial, Type A, B, C, D, E, G, H & J
Discount Schedule	CP7G
Article Number	785901064442
Package Quantity	1
Weight	8.67 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.