

Product availability: Stock - Normally stocked in distribution facility

Main

Commercial Status	Commercialised
Range of product	TeSys D TeSys D control relay
Device short name	LAD4
Product or component type	Suppressor module
Product compatibility	LC1D09...D38 LC1DT20...DT40

Complementary

Mounting location	Side
Mounting mode	By clips
Suppressor technology	Flywheel diode
Control circuit voltage	24...250 V DC
Maximum peak voltage	1 Uc
Product weight	0.03 lb(US) (0.012 kg)

Environment

Ambient air temperature for operation	-13...131 °F (-25...55 °C)
Ambient air temperature for storage	-40...176 °F (-40...80 °C)

Ordering and shipping details

Category	22399 - TESYS U, ACCESSORIES
Discount Schedule	I11
GTIN	00785901825838
Nbr. of units in pkg.	1
Package weight(Lbs)	0.02
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	FR

Contractual warranty

Period	18 months
--------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.