

Product data sheet


Characteristics

LAD6K10B

auxiliary latch block TeSys - 24 V DC/AC 50...60 Hz

Product availability: Stock - Normally stocked in distribution facility

Price*: 77.00 USD



Main

Commercial Status	Commercialised
Range of product	TeSys D TeSys D control relay
Product or component type	Mechanical latch block
Product compatibility	LC1D09...D38 LC1D40A...D65A LC1DT20...DT40 LC1DT60A...DT80A TeSys D control relays
Control circuit voltage	24 V AC 50/60 Hz 24 V DC

Complementary

Mounting location	Front side
Tripping control	Electrical Manual
[Ui] rated insulation voltage	690 V - conforming to IEC 60947-5-1
Power required in VA	25 for AC circuit
Power required in W	30 W for DC circuit
Mechanical durability	500000 cycles
Operating rate	1200 cyc/h
On-load factor	10 %
Product weight	0.15 lb(US) (0.07 kg)

Environment

Product certifications	CSA UL
IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for operation	-13...131 °F (-25...55 °C)
Ambient air temperature for storage	-40...176 °F (-40...80 °C)

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901454915
Nbr. of units in pkg.	1
Package weight(Lbs)	0.22
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	FR

Contractual warranty

Period	18 months
--------	-----------
