



## OK435/12 NYLP

12 pole natural polyamide PA6.6 wire protected pillar terminal block 14.5mm pitch 57a 450v



### SPECIFICATION

<b>Number of Poles</b>	12
<b>Terminal Material</b>	OT58 nickel plated
<b>Terminal Type</b>	Wire Protected
<b>Body Material</b>	Polyamide PA6.6
<b>Colour</b>	Natural
<b>Glow Wire Resistance Test Temp</b>	GWIT775°C (EN60695-2-13)
<b>Max Conductor Size (Sq mm)</b>	10
<b>Max Current (A)</b>	57
<b>Max Voltage (V)</b>	450
<b>Working Temperature</b>	110
<b>Pitch (mm)</b>	14.5
<b>Height (mm)</b>	24.8
<b>Width (mm)</b>	31.8
<b>Length (mm)</b>	171.2
<b>Diameter (mm)</b>	5.8
<b>Terminal Screw Material</b>	White zinc plated steel
<b>Wire Protection Material</b>	Stainless steel