




MAINS VOLTAGE:
No Driver Required

LED TRIANGLE CABINET DOWNLIGHT

- 30,000 hours average rated life: reduced lamp replacement cycle
- 3000K warm colour temperature: offering a pleasing lighting appearance
- 1.7W = 160 lumens: ideal low energy solution to standard halogen cabinet lights
- Not suitable for use with dimmers
- Prewired with 2m mains cable and no separate driver required: facilitating easy installation
- Visually similar to 20W G4 halogen

• M.O.M: 1 / O.P.Q: 40



Code	Colour	Wattage	Colour Temp.	Lumens	Avg. Rated Life (Hrs)	Energy Rating
CLEDTRI	Brushed Nickel	1.7W	3000K	160 lm	30,000 hrs	A ⁺


Eterna

CLEDTRI



This luminaire contains built-in LED lamps.



LED

The lamps cannot be changed in the luminaire.

874/2012



LAMP SPECIFICATIONS:

Lumens total flux	160 lm
Lumens 90° flux	150 lm
Rated Wattage	1.7W
Rated luminous flux	150 lm
Nominal life time of the lamp	30,000 hrs
Colour temperature	3000K
Number of switching cycles before premature lamp failure	15,000
Warm-up time up to 60 % of the full light output	Instant full light
Dimmable	No
Lamp dimensions (Ø)	40mm
Nominal beam angle	90°
Rated power	1.7W
Rated lamp lifetime	30,000 hrs
Lamp power factor	0.263
Lumen maintenance factor at end of nominal life	>70%
Starting time	<0.5s
Colour rendering	>80
Colour consistency	Within 6 step Macadam ellipse
Rated peak intensity	48.2cd
Rated beam angle	90°
Voltage	240V

Not suitable for accent lighting