




T5 FITTINGS ALL INCLUDE REVERSE POLARITY PROTECTION
 To ensure compliance, our link system is polarised ensuring live & neutral cannot be reversed throughout a linked installation

This luminaire contains built-in LED lamps.



The lamps cannot be changed in the luminaire.

874/2012




LINKABLE LED STRIP LIGHTS

Long life, energy efficient alternative to traditional fluorescent under cabinet lights.

- Superb light output and lighting effect: low power consumption with enhanced life expectancy
- 1.8m mains lead with 0.3m link lead: linkable with up to 5 other fittings
- To ensure compliance, our link system is polarised ensuring live & neutral cannot be reversed throughout a linked installation
- Optically optimised diffuser: ensures a soft diffused light with no degradation of light output
- Polycarbonate construction
- 3000K warm colour temperature: offering a pleasing lighting appearance
- See product codes NL1WH / NL50WH / NL25WH for additional link leads
- Rocker switch

- **T5LED4 / T5LED8** = M.O.M: 1 / O.P.Q: 40
- **T5LED10** = M.O.M: 1 / O.P.Q: 30
- **Link Leads** = M.O.M: 5 / O.P.Q: 200



| LAMP SPECIFICATIONS: | T5LED4 | T5LED8 | T5LED10 |
|--|-------------------------------|-------------------------------|-------------------------------|
| Lumens total flux | 360 lm | 680 lm | 900 lm |
| Lumens 120° flux | 335 lm | 632 lm | 837 lm |
| Rated Wattage | 4W | 8W | 10W |
| Rated luminous flux | 335 lm | 632 lm | 837 lm |
| Nominal life time of the lamp | 25,000 hrs | 25,000 hrs | 25,000 hrs |
| Colour temperature | 3000K | 3000K | 3000K |
| Number of switching cycles before premature lamp failure | 12,500 | 12,500 | 12,500 |
| Warm-up time up to 60 % of the full light output | Instant full light | Instant full light | Instant full light |
| Dimmable | No | No | No |
| Lamp dimensions (L) | 338mm | 608mm | 908mm |
| Nominal beam angle | 120° | 120° | 120° |
| Rated power | 4W | 8W | 10W |
| Rated lamp lifetime | 25,000 hrs | 25,000 hrs | 25,000 hrs |
| Lamp power factor | >0.4 | >0.5 | >0.5 |
| Lumen maintenance factor at end of nominal life | 70% | 70% | 70% |
| Starting time | <0.5s | <0.5s | <0.5s |
| Colour rendering | ≥80% | ≥80% | ≥80% |
| Colour consistency | Within 6 step Macadam ellipse | Within 6 step Macadam ellipse | Within 6 step Macadam ellipse |
| Rated peak intensity | 108cd | 204cd | 270cd |
| Rated beam angle | 120° | 120° | 120° |
| Voltage | 230V | 230V | 230V |

Not suitable for accent lighting

| Code | Length / Version | Colour | Wattage | Colour Temp. | Lumens | Avg. Rated Life (Hrs) | Energy Rating |
|---------|------------------|--------|---------|--------------|--------|-----------------------|---------------|
| T5LED4 | 338mm Fitting | White | 4W | 3000K | 360 lm | 25,000 hrs | A+ |
| T5LED8 | 608mm Fitting | White | 8W | 3000K | 680 lm | 25,000 hrs | A+ |
| T5LED10 | 908mm Fitting | White | 10W | 3000K | 900 lm | 25,000 hrs | A+ |
| NL1WH | 1M Lead | White | - | - | - | - | - |
| NL50WH | 500mm Lead | White | - | - | - | - | - |
| NL25WH | 250mm Lead | White | - | - | - | - | - |