




This luminaire contains built-in LED lamps.



The lamps cannot be changed in the luminaire.

874/2012



**LED LAMP SPECIFICATIONS:**


Lumens total flux	<b>3500 lm</b>
Rated Wattage	50W
Rated luminous flux	3500 lm
Nominal life time of the lamp	25,000 hrs
Colour temperature	4000K
Number of switching cycles before premature lamp failure	≥12,500
Warm-up time up to 60 % of the full light output	Instant full light
Dimmable	No
LED dimensions (W/H)	23 x 34mm
Nominal beam angle	120°
Rated power	50W
Rated lamp lifetime	25,000 hrs
Lamp power factor	>0.9
Lumen maintenance factor at end of nominal life	<70%
Starting time	<0.5s
Colour rendering	>70
Colour consistency	Within 6 step Macadam ellipse
Rated peak intensity	1170cd
Rated beam angle	120°
Voltage	240V

Not suitable for accent lighting

**50W LED FLOODLIGHT**

- High Power COB LED Chip: which is better suited to these higher power ratings, where the large physical size of the housing and chip array maximises performance available from this chip technology
- 4000K colour temperature: bright light without the harsh effect of higher colour temperature products
- Die cast aluminium construction
- Pre-wired with 80cm of cable
- IES file available

• M.O.M: 1 / O.P.Q: 4



Code	Colour	Wattage	Colour Temp.	Lumens	Avg. Rated Life (Hrs)	IP Rating	Energy Rating
FLOOD50	Black	50W	4000K	3500 lm	25,000 hrs	IP44	A

