

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0016020069](#)  
**Status:** **Active**  
**Overview:** C-Grid® Products  
**Description:** SL™ Crimp Terminal, Series 70058, Female, with Tin (Sn) Plated Contact, 24-30 AWG, Reel

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-70400 (PDF)</a>
<a href="#">Product Specification PS-51008-002 (PDF)</a>	<a href="#">Test Summary TS-70058-001 (PDF)</a>
<a href="#">Product Specification PS-70058 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Terminals
Series	<a href="#">70058</a>
Application	Signal
Comments	Use with CyClone Panel-to-Panel Connector <a href="#">73099</a>
Crimp Quality Equipment	Yes
Overview	<a href="#">C-Grid® Products</a>
Packaging Alternative	<a href="#">16-02-0096 (Loose)</a>
Product Name	SL™
UPC	800753595941

**Physical**

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.073/g
Packaging Type	Reel
Plating min - Mating	3.810µm
Plating min - Termination	1.905µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52mm max.
Wire Size AWG	24, 26, 28, 30
Wire Size mm²	N/A

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

Old Part Number	70058-0004
-----------------	------------

**Reference - Drawing Numbers**

Product Specification	PS-51008-002, PS-70058, PS-70400
Sales Drawing	SD-70058-0004
Test Summary	TS-70058-001



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Contains SVHC(2015 June 15): No

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

**Search Parts in this Series**

[70058 Series](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
T2 Terminator	<a href="#">0639103100</a>
Tooling Die	
Insertion Tool	<a href="#">0011020022</a>
FineAdjust™	<a href="#">0639001500</a>
Applicator, 24-30 AWG Wire	
Hand Crimp Tool For SL™ Crimp Terminals	<a href="#">0638258800</a>
FineAdjust™	<a href="#">0639003100</a>
Applicator for Female	

Crimp Terminal,  
24-30 AWG Wire

**Japan**

<b>Description</b>	<b>Product #</b>
Side-Feed Applicator For Full-Auto Machine	<u>0570143200</u>
Applicator for M211A Bench Press, 22-30 AWG Wire	<u>0570143000</u>
Hand Insertion Tool	<u>0570336000</u>

This document was generated on 10/13/2015

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**